




客户图



Note:

1: Material(材料):

Housing: PA9T(胶芯:PA9T)

Pin: Brass C3604 (针体: 黄铜 C3604)

Magnet: NdFeB (磁铁: 钕铁硼)

2: Plating(电镀):

Pin: 3u' Au over 50u'~80u' Ni

(针体: 镀金3u', 镍底50u'~80u'.)

Magnet: Ni plated (磁铁: 镀镍)

3: Electrical(电气特性):

Insulation Resistance: 1,000MΩ minimum.

(绝缘电阻: 1,000MΩ以上)


Dielectric Withstand Voltage: 500VAC/minute.

(抗击电压: 500VAC/minute)

4: WorkTemperature(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -20℃~ +70℃



深圳市鑫扬泽电子有限公司



TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2021.7.2	VER.	A.1

THE UNMARKED TOLERANCE ARE AS BELOW:

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZT0675-20048-02025-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			