


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS




Technical drawing of a mechanical part with dimensions and a surface texture symbol.

Dimensions:

- Overall width: 3.16
- Overall height: 1.20
- Overall length: 2.10
- Internal width: 1.20
- Internal height: 0.80
- Internal length: 4.00
- Internal width (right): 1.60

Surface texture symbol: $\sqrt{0.10}$




TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10*	PART NO.	TITLE: TYPEC母座16PIN长6.5MM 外壳带弹沉板1.6 (CH=0.00)			
.XX ±0.20	.X* ± 8*	101002-211010				
.XXX ±0.10	.XX* ± 5*	DESIGN: JANUS	DRAWG NO. C-101002			
UNIT	mm					
MATERIAL	---	CHED: JANUS		SCALE	SHEET	REV.
FINISH	---	APPD: ARAY		1:1	1/3	A

This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS


RoHS & HF
Compliant



AFTER MATING

USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND



RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.80MM;DEFAULT TOLERANCE:±0.05

ORDER INFORMTION

P/N: 101002-211010

CONTACT FUNCTIONAL AREA PLATED
01: Au G/F



CONTACT SOLDER AREA PLATED
1: Au G/F

PACKAGING
1: REEL PACKAGING

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD		
X.X	±0.30	X.*	±10°	PART NO.	TITLE: TYPEC母座16PIN长6.5MM 外壳带弹沉板1.6 (CH=0.00)
.XX	±0.20	.X*	± 8°	101002-211010	
.XXX	±0.10	.XX*	± 5°	DESIGN: JANUS	
UNIT	mm			CHED: JANUS	DRAWG NO.
MATERIAL	---			APPD: ARAY	C-101002
FINISH	---				SCALE SHEET REV.
					1:1 2/3 A

This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS



		REEL	CARTON
CONNECTOR (PCS)		1400	14000
TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING XSUA ® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD	
X.X	±0.30	X.*	±10'
.XX	±0.20	.X.*	± 8'
.XXX	±0.10	.XX.*	± 5'
UNIT	mm	PART NO.	101002-211010
MATERIAL	---	DESIGN:	JANUS
FINISH	---	CHED:	JANUS
		APPD:	ARAY
		TITLE: TYPEC母座16PIN长6.5MM 外壳带弹沉板1.6 (CH=0.00)	
		DRAWG NO. C-101002	
		SCALE	SHEET
		1:1	3/3
		REV.	A