




客户图



Note:

1: Material(材料):

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

Terminal: Brass C3604 (端子: 黄铜 C3604)

2: Plating(电镀):

Barrel: 5u' Au over 200u' Cu over 200u' Ni(针管: 镀金5u', 铜底200u', 镍底200u'.)

Plunger: 5u' Au over 200u' Cu over 200u' Ni(针头: 镀金5u', 铜底200u', 镍底200u'.)

Spring: No plated (弹簧: 不电镀)

Terminal: 5u' Au over 200u' Cu over 200u' Ni(端子: 镀金5u', 铜底200u', 镍底200u'.)

3: Electrical(电气特性):

Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)

Contact Resistance: 100 mohm Max. at working height.

接触电阻: 最大100毫欧 (在工作高度状态下)

4: Mechanical(机械性能):

Force: 80g±20% at working height. (80g±20% 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -20℃~ +70℃

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2024.7.26	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZR0232-30058-02
CHECKED BY:		TITLE:	Pogo pin连接器
APPROVED BY:			