


NO.	ECN NO.	DESCRIPTION	DATE

客户图



- Note:
- 1: Material(材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
 - 2: Plating(电镀):
Barrel: 1u' Au over 80~120u' Cu over 50~100u' Ni (针管: 镀金1u', 铜底80~120u', 镍底50~100u'.)
Plunger: 1u' Au over 80~120u' Cu over 50~100u' Ni (针头: 镀金1u', 铜底80~120u', 镍底50~100u'.)
Spring: No plated (弹簧: 不电镀)
 - 3: Electrical(电气特性):
Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
 - 4: Mechanical(机械性能):
Force: 250g $\pm$ 20% at working height. (250g $\pm$ 20% 在工作高度)。
Durability: 10.000 cycles(min) (寿命: 10000次)
 - 5: WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: -20℃~ +70℃

深圳市鑫扬泽电子有限公司



HTTP://WWW.XYZPOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.	YZR0228-35215-01
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE		CHECKED BY:		TITLE:	Pogo pin连接器
DATE:	2013.03.01	VER.	D.0	X.XX	± 0.05 mm	X.XX	$\pm 0.50^\circ$	APPROVED BY:			
				X.X	± 0.10 mm	X.X	$\pm 1.00^\circ$				
				X.	± 0.20 mm	X.	$\pm 2.00^\circ$				