





ABIDE BY ROHS

ITEM	H
01	3.5
02	3.8
03	4.3
04	4.5
05	5.0
06	5.5
07	6.0
08	6.5
09	7.0
10	7.5
11	8.0
12	8.5
13	...
14	10.0

* Key size



P.C.B 布局
Recommended PCB Layout



线路图
Circuit Diagram

Remarks:

1. Rated current、Voltage: DC 12V 50mA
2. Contact resistance: $\leq 100\text{m}\Omega$
3. Insulation resistance: $\geq 100\text{M}\Omega$
4. The intensity of operations: $260\pm 50\text{gf}$
5. Open and close the trip: $0.2\pm 0.1\text{mm}$
6. Life requirements: 100,000次
7. Withstand voltage: AC 250V 1分钟
8. All materials comply with RoHS standards

5	Cover	Brass	1	Cu-Sn Plating
4	Shrapnel	SUS	1	Ag Plating
3	Terminal	Brass	2	Ag Plating
2	Button	PPA	1	Black
1	Housing	PPA	1	Black
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE	浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.			
绘图 DRAWN		X≤1 ±0.05	产品名称 轻触开关			
设计 DESIGN		1≤X≤5 ±0.10				
审核 CHECKED		5≤X≤10 ±0.15				
校准 STANDARD		X>10 ±0.25				
批准 APPROVALS		ANGLE ±3°	产品型号 MODEL	4.5*4.5前插后贴		
		图号 DRAWING NO.	产品编码 PART NO	ES414X-10X-XXX-26-B		
		重量 WT.	视角 PROJ	比例 SCALE	页码 SHEET	1 OF 1

ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	--------------	---------	--------	--------