





客户图



RECOMMENDED PCB LAYOUT

Note:

1: Material(材料):

Housing: PA9T(胶芯:PA9T)

Pin: Brass C3604 (针体: 黄铜 C3604)

Magnet: NdFeB (磁铁: 钕铁硼)

2: Plating(电镀):

Pin: 3u' Au over 50u'~80u' Ni

(针体: 镀金3u', 镍底50u'~80u'.)

Magnet : Zc plated (磁铁: 镀锌)

3: Electrical(电气特性):

Insulation Resistance: 1,000MΩ minimum.

(绝缘电阻: 1,000MΩ以上)

Dielectric Withstand Voltage: 500VAC/minute.

(抗击电压: 500VAC/minute)

4: WorkTemperature(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -20℃~ +70℃

深圳市鑫扬泽电子有限公司



TEL:0755-28773277 FAX:0755-28891353

SCALE: N/A

UNIT

mm

SHEET: 1 of 1

PROJECTION



DATE: 2022.3.24

VER.

A.1

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH

X.XX ±0.05mm
X.X ±0.10mm
X. ±0.20mm

ANGLE

X.XX ±0.50°
X.X ±1.00°
X. ±2.00°

DESIGNED BY:

DWG. NO.

YZT0675-20048-03025-01

CHECKED BY:

TITLE:

Pogo pin 连接器

APPROVED BY: