






SECTION A-A








AFTER MATING




品贊科技

Switch



SECTION B-B



G-Switch USB-C Specification:

- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
- 2.Withstanding voltage: 100V AC/minute
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force: 5N~20N
- 7.Unmating force: 8N~20N
- 8.Durability cycle:10,000 cycles
- 9.Waterproof grade: IP-X8
- 10.Compliant with: IEC62680-1-3

USB IF TID:13003

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First


NO.	NAME	MATERIAL	REMARKS
5	GLUE	EPOXY RESIN	COLOR:BLACK
4	LIM_RING	SILICA GEL	NA
3	OUT SHELL	STAINLESS STEEL	NI30u" MIN PLATED
2	INNER SHELL	STAINLESS STEEL	NO PLATING
1	INSERT MD	MID PLATE STAINLESS STEEL CONTACT:COPPER ALLOY HIGH TEMPERATURE PLASTIC	NO PLATING Au1u"MIN PLATED ON CONTACT AREA COLOR:BLACK,UL94V_0



SCALE:	UNIT: mm	Title: IPX8 Vertical Type-c 16P Female SMT H=7.5mm			
SIZE: A4		Molde Code: GT-USB-9113B			
Unless otherwise General Tolerance: X. ±0.40 X.x ±0.30 X.xx ±0.20 X.xxx ±0.10 X* ±5°		DRAWN	CHECKED	APPROVED	DATE
		Xla	Chen	Chen	2024.11.13



REV: A1 SHEET: 1/2





G-Switch USB-C Specification:

- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
- 2.Withstanding voltage: 100V AC MAX
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force: 5N~20N
- 7.Unmating force: 8N~20N
- 8.Durability cycle:10,000 cycles
- 9.Waterproof grade: IP-X8
- 10.Compliant with: IEC62680-1-3


USB IF TID:13003

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First

B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First



RECOMMENDED PCB LAYOUT
SCALE 2/1 TOLERANCE:±0.05



SCALE:	UNIT: mm	Title: IPX8 Vertical Type-c 16P Female SMT H=7.5mm			
SIZE: A4		Molde Code: GT-USB-9113B			
Unless otherwise General Tolerance:		DRAWN	CHECKED	APPROVED	DATE
X.	±0.40	Xia	Chen	Chen	2024.11.13
X.x	±0.30				
X.xx	±0.20				
X.xxx	±0.10				
X°	±5°				



NO.	NAME	MATERIAL	REMARKS
5	GLUE	EPOXY RESIN	COLOR:BLACK
4	LIM_RING	SLILICA GEL	NA
3	OUT SHELL	STAINLESS STEEL	Ni30u" MIN PLATED
2	INNER SHELL	STAINLESS STEEL	NO PLATING
1	INSERT MD	MID PLATE STAINLESS STEEL	NO PLATING
		CONTACT:COPPER ALLOY	Au1u"MIN PLATED ON CONTACT AREA
		HIGH TEMPERATURE PLASTIC	COLOR:BLACK,UL94V_0

E

E