

RoHS

目錄
MAPX设变内容
MODIFICATION日期
DATE

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voitage:
500 V AC AT Sea Levot
5. 绝缘阻抗: Lnsulation Resistance:
1000MEGA ohms MIN


物理性能: Mechanical:

1. 插拔力: Cnnector Mate and Unmate Force
Mate force: 3.57kgf (MAX)
Unmate force: 1.02kgf (MIN)
2. 端子保持力: Terminal Retenion
1.0kgf (MIN)





3. 寿命: 1500次

原材料: Matorial:

1. 塑胶: Housing: pbt /lcp
 2. 端子: Contact: Copper Alloy C2680
 3. 外壳: Shell: SPCC/c2680
- 电镀: Finish:
1. 端子Contact: Au G/F u" Plated on contact area
Tin50u" Plated on solder area
Nickel 30u" Plated underplating over all.
 2. 外壳Shell: Nickel 50u" Min plating over all.
 3. Temperature Range: -55° C to +85° C



P.C.B LAYOUT



Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.35	X'.	±5°
.X	±0.30	.X'	±2°
.XX	±0.25	.XX'	±1°
.XXX	±0.10	.XXX'	±0.5°

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	Erick	产品料号 PRODUCT PART NO.	909-161A1025D10102
比例 SCALE	1:1	审核 CHKD	L S S	产品名称 PRODUCT NO.	AF90度10.0短体前两脚无边 铁壳PBT黑胶加高7.8MM
日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW	版本 VER