

6 5 4 3 2 1


This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS

RoHS & HF
Compliant

USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TXp1	B11	RXp1
A3	TXn1	B10	RXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RXn2	B3	TXn2
A11	RXp2	B2	TXp2
A12	GND	B1	GND



RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 1.00MM;DEFAULT TOLERANCE:±0.05

P/N: 101032-211030

CONTACT FUNCTIONAL AREA PLATED
03: Au 3U*







CONTACT SOLDER AREA PLATED
1: Au G/F


PACKAGING
1: REEL PACKAGING

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING		XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X	±0.30	X.* ±10°	PART NO.	TITLE: TYPEC母座24PIN双壳长8.25MM (CH=2.0) 40G			
.XX	±0.20	.X.* ± 8°	101032-211030				
.XXX	±0.10	.XX.* ± 5°	DESIGN: JANUS	DRAWG NO. C-101032			
UNIT	mm	CHED: JANUS					
MATERIAL	---	APPD: ARAY			SCALE	SHEET	REV.
FINISH	---				1:1	2/3	A

This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

RoHS & HF
Compliant



			REEL	CARTON		
		CONNECTOR (PCS)	700	7000		
TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: TYPEC母座24PIN双壳长8.25MM (CH=2.0) 40G			
.XX ±0.20	.X* ± 8°	101032-211030				
.XXX ±0.10	.XX* ± 5°					
UNIT	mm	DESIGN: JANUS	DRAWG NO.			
MATERIAL	---	CHED: JANUS	C-101032			
FINISH	---	APPD: ARAY		SCALE 1:1	SHEET 3/3	REV. A