



客户图



外观面



技术要求:

- 1.材料 无铅铜 C6801;
- 2.不允许有批锋,毛刺;切断点最大不超过0.03mm.
- 3.镀金3u',铜底80-120u',镍底120-200u'.

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2025.5.13	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZT1168-25025-G3
CHECKED BY:		TITLE:	车件
APPROVED BY:			