




客户图



Note:

1: Material (材料):

Housing: PA46, Colour Code RAL3028 (胶芯: PA46, 色号RAL3028)

Pin: Brass C3604 (针体: 黄铜 C3604)

Magnet: NdFeB (磁铁: 钕铁硼)

2: Plating (电镀):

Pin: 3u' Au over 50u'~80u' Ni (针体: 镀金3u', 镍底50u'~80u'.)

Magnet: Nickel plating (磁铁: 镀镍)

3: Electrical (电气特性):

Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)



Insulation Resistance: 1,000MΩ minimum. (绝缘电阻: 1,000MΩ以上)

Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)

4: WorkTemperature (工作环境):

Withstanding Hight Temperature: 280℃

Operational Temperature: -20℃~+70℃



RECOMMENDED PCB LAYOUT

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2024.6.19	VER.	A.1

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZT0675-20046-05025-02
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			