





客户图

NO.	CON NO.	DESCRIPTION	DATE



RECOMMENDED PCB LAYOUT



Note:

- Material(材料):
Housing: PA46 (胶芯: PA46)
Pin: Brass C3604 (针体: 黄铜 C3604)
- Plating(电镀):
Pin: 3u' Au over 50~80u' Ni (针体: 镀金3u', 镍底50~80u'.)
- Electrical(电气特性):
Insulation Resistance: 1,000M Ω minimum.
(绝缘电阻: 1,000M Ω 以上)
Dielectric Withstand Voltage: 500VAC/minute.
(抗击电压: 500VAC/minute)
- WorkTemperature(工作环境):
Withstanding Higt Temperature: 280 $^{\circ}$ C
Operational Temperature: - 40 $^{\circ}$ C ~ + 85 $^{\circ}$ C

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2023.11.20	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	$\pm 0.05\text{mm}$	X.XX	$\pm 0.50^{\circ}$
X.X	$\pm 0.10\text{mm}$	X.X	$\pm 1.00^{\circ}$
X.	$\pm 0.20\text{mm}$	X.	$\pm 2.00^{\circ}$

DESIGNED BY:		DWG. NO.	YZT0159-20092-02076-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			