


This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS


RoHS & HF
Compliant



AFTER MATING

USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TXp1	B11	RXp1
A3	TXn1	B10	RXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RXn2	B3	TXn2
A11	RXp2	B2	TXp2
A12	GND	B1	GND



RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.60MM;DEFAULT TOLERANCE:±0.05

P/N: 101010-211010

CONTACT FUNCTIONAL AREA PLATED
01: Au 1u"





CONTACT SOLDER AREA PLATED
1: Au G/F

PACKAGING
1: REEL PACKAGING

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: TYPEC母座24PIN长7.9MM 板上脚长0.6 (CH=1.68)			
.XX ±0.20	.X.* ± 8°	101010-211010				
.XXX ±0.10	.XX.* ± 5°	DESIGN: JANUS	DRAWG NO. C-101010			
UNIT	mm					
MATERIAL	---	CHED: JANUS	 SCALE SHEET REV.			
FINISH	---	APPD: ARAY				
			1:1	2/3	A	

This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS



		REEL	CARTON
CONNECTOR (PCS)		900	9000
TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	
X.X	±0.30	X.*	±10*
.XX	±0.20	.X.*	± 8*
.XXX	±0.10	.XX.*	± 5*
UNIT	mm	DESIGN:	JANUS
MATERIAL	---	CHED:	JANUS
FINISH	---	APPD:	ARAY
PART NO.		TITLE:	
101010-211010		TYPEC母座24PIN长7.9MM 板上脚长0.6 (CH=1.68)	
DRAWG NO.		C-101010	
		SCALE	SHEET
		1:1	3/3
		REV.	A