












RECOMMENDED P.C. BOARD PATTERN DIM. (REF.)



2P



3P



MATED CONNECTORS

NOTES:

1. MATERIAL:
HOUSING: HIGH-TEMP PLASTIC,UL 94-V0,COLOR:NATURE ;
CONTACT: COPPER ALLOY;
LEG: COPPER ALLOY;
2. PLATING:
CONTACT: GOLD OR TIN PLATED ON NICKEL OVERALL.
LEG: GOLD OR TIN PLATED ON NICKEL OVERALL.
3. RATING:
CURRENT RATING: 1.0A AC/DC
VOLTAGE RATING: 125V AC/DC
TEMPERATURE RANGE: -45°C~+105°C;

CKT	Dim A	Dim B	Dim C
2	1.25	2.87	7.65
3	2.50	4.12	8.90
4	3.75	5.37	10.15
5	5.00	6.62	11.40
6	6.25	7.87	12.65
7	7.50	9.12	13.90
8	8.75	10.37	15.15
9	10.00	11.62	16.40
10	11.25	12.87	17.65
11	12.50	14.12	18.90
12	13.75	15.37	20.15
13	15.00	16.62	21.40
14	16.25	17.87	22.65
15	17.50	19.12	23.90
16	18.75	20.37	25.15
17	20.00	21.62	26.40
18	21.25	22.87	27.65
19	22.50	24.12	28.90
20	23.75	25.37	30.15

修改焊脚形状和尺寸	'23/10/21	
新图制成	'23/06/03	
REV	REVISION DESCRIPTION	DATE SIGNATURE

一般公差
TOLERANCES
X ±0.5 XX ±0.15
X ±0.25 XXX ±0.1
ANGLES ±2°

檢驗尺寸標示
SYMBOLS ① ② INDICATE
CLASSIFICATION DIMENSION
① MARK IS CRITICAL DIM.
② MARK IS MAJOR DIM.
表面處理 (FINISH)

广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO.,LTD

品名 (TITLE)
1.25超薄卧贴

圖號 (DWG.NO)
1.25T-CB-NPWB-R-GF

比例 (SCALE)
4:1

單位 (UNITS)
mm

張數 (SHEET)
1 OF 1

SIZE
A4

REV
A

製圖 (DR)
'23/06/03
審核 (CHKD)

核准 (APPD)