



REV.	ECN NO	LTR	DESCRIPTION	REVISER	DATE



规格说明:Specifications:

电气特性:Electrical:

- 额定电流: Current Rating
1.5A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触阻抗:Contact Resistance
30 milliohms MAX
- 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levol
- 绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:



- 插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:1.02kgf (MIN)
- 端子保持力: Terminal Retenion
1.0kgf (MIN)

原材料:Matarial:

- 塑胶:Housing:
Hing Temperature Tnermaplastics,
U1 94V-0 PBT White/Black
- 端子:Contact:Copper Alloy C2680 T:0.2mm
- 外壳:Shell: SPCC T:0.3mm

电镀:Finish:

- 端子:Contact: Piated Gold in Mating Area;
Tin On Solder Talls
Sn≥100U" Ni≥40U" Au:1U"
- 外壳:Shell: Nickel Plating
Ni≥50U"



膜厚测试点

产品图				深圳市金航标电子有限公司					
PRODUCT CHART DWG				www.kinghelm.com.cn					
公差一览表				0755-28190160					
TOLERANCE UNLESS OTHERMSE				单位	MM	制图	制图料号	KH-AF90CB-13.6JB	
X.	±0.25	X.	±5.°	UNITS		DRAWING	PRODUCT PART NO.		
.X	±0.20	.X	±2.°	比例	1:1	审核	产品名称	USB A/F 沉板带翅膀 直脚 卷边端子DIP	
.XX	±0.15	.XX	±1.°	SCALE		CHKD	PRODUCT NO.		
.XXX	±0.10	.XXX	±0.5°	日期	2022.03.27	核准	角法	版本	AO
				DATE		APPD	VIEW	VER	