
















品质管控等级要求		
符号	等级	产品管控要求
▼	重点要求	巡检，定义检验频率
▽	特殊性要求	CPK>1.33
⊙	全检要求	自动机检验

UNLESS OTHERWISE SPECIFIED TOLERANCES		 深圳市精睿兴业科技有限公司 SHENZHEN KRCONN TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	Type.C 8PIN Vertical DIP TYPE CONN. RECEPTACLE		
X :±0.5	X :±2°	DWN	chenjun	PART NO. TCR59-61120805-05	
X.X :±0.30	X.X :±1°	CHKD	chenjun	SCALE:1:1	UNIT: mm
X.XX :±0.20		APVD	Kevin.d	SIZE: A4	SHEET:10F1
X.XXX :±0.10		DRAW NO. C-DWG-TCR59-07			CUSTOMER COPY



REV.	ECN NO OR DESCRIPTION	REVISED	DATE
A	PROPOSE ONLY	ERIC	2022.12.06
B	UPDATE DRAWING	ERIC	2022.11.30



PRODUCT ORDER



(SC 2:1)
RECOMMENDED PCB LAYOUT(THICKNESS:0.80MM)
PWB TOLERANCE: ±0.05

UNLESS OTHERWISE SPECIFIED TOLERANCES		 深圳市精睿兴业科技有限公司 SHENZHEN KRCONN TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	Type.C 8PIN Vertical DIP TYPE CONN. RECEPTACLE		
X :±0.5	X :±2°	DWN	chenjun	PART NO. TCR59-61120805-05	
X.X :±0.30	X.X :±1°	CHKD	chenjun	SCALE:1:1	UNIT: mm
X.XX :±0.20		APVD	Kevin.d	SIZE: A4	
X.XXX :±0.10		DRAW NO. C-DWG-TCR59-07			CUSTOMER COPY






REV.	ECN NO OR DESCRIPTION	REVISED	DATE
A	PROPOSE ONLY	ERIC	2022.01.18
B	UPDATE DRAWING	ERIC	2022.11.30

CONN. PART NO.	CONN. QTY./REEL	REEL QTY./CARTON	CONN. QTY./CARTON
TCR59-61120805-05	600	10	6000 PCS



CUSTOMER TO USE DIRECTION PULL OUT DIRECTION (出料方向)

TOTAL 10LAYERS



UNLESS OTHERWISE SPECIFIED TOLERANCES				深圳市精睿兴业科技有限公司 SHENZHEN KRCONN TECHNOLOGY CO., LTD			
DECIMALS:		ANGLES:		TITLE Type.C 8PIN Vertical DIP TYPE CONN. RECEPTACLE			
X	:±0.5	X	:±2°	DWN	chenjun	PART NO. TCR59-61120805-05	
X.X	:±0.30	X.X	:±1°	CHKD	chenjun	SCALE:1:1	UNIT: mm
X.XX	:±0.20			APVD	Kevin.d	SIZE: A4	SHEET:10F1
X.XXX	:±0.10						REV: B
				DRAW NO. C-DWG-TCR59-07		CUSTOMER COPY	