


ROHS




REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术指标(Technical Index):



1. 塑件材质: LCP UL94-V0
2. 端子材质: 磷青铜, 镀锡/镀金
3. 焊片材质: 磷青铜, 镀锡/镀金
4. 温度范围(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
5. 额定电压(Rated voltage): 50V, AC/DC(=等效).
6. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
7. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
8. 耐压: 200V/1 Minute.



18PIN



SECTION A-A



PCB Layout

CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING			TITLE	FPC连接器1.0间距18PIN抽屉式下接（卧贴）	REV.	A
CHECKED						
APPROVED						
TOLERANCES ARE			PART NO.	LAIL-FPC-BX01-18P1.0-W	UNITS	mm
30-150	±0.35	ANGLE				
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			DWG. NO.		Projection	