





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- 技术指标(Technical Index):
1. 塑件材质: LCP UL94-V0
 2. 端子材质: 磷青铜, 镀锡/镀金
 3. 焊片材质: 磷青铜, 镀锡/镀金
 4. 温度范围(Temperature range): -25° C~85° C.
 5. 额定电压(Rated voltage): 50V, AC/DC(=等效).
 6. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
 7. 绝缘电阻(Insulation resistance): $\geq 500M\Omega$.
 8. 耐压: 200V/1 Minute.

22PIN



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司						
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD						
CHECKED								
APPROVED								
TOLERANCES ARE		TITLE		REV.	A			
30-150 ±0.35		FPC连接器0.5间距22PIN抽屉式单侧触点/垂直(立贴)						
10-30 ±0.2		PART NO.	LAIL-FPC-BL01-22P0.5-LT	UNITS	mm			
5-10 ±0.15		DWG. NO.		Projection				
0-5 ±0.1								
ANGLE								
±3°								