

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

1. MATERIAL:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC(UL94V-0), COLOR: NATURAL.

CONTACTS: COPPER ALLOY.

PEG: COPPER ALLOY.

ACTUATOR: HIGH TEMPERATURE THERMOPLASTIC(UL94-V0).

2. RATING:

OPERATING VOLTAGE: 50Vrms AC.

CURRENT RATING: 0.5A.

OPERATING TEMPERATURE: $-55^{\circ}\text{C}\sim+85^{\circ}\text{C}$.


OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

STORAGE TEMPERATURE RANGE: $-10^{\circ}\text{C}\sim+50^{\circ}\text{C}$.





STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

INSULATION RESISTANCE $\geq 500\text{M}\Omega$.

WITHSTAND VOLTAGE: 200V/1 MINUTE.



16PIN



CUSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司	
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD	
CHECKED			
APPROVED			
TOLERANCES ARE		TITLE	FPC连接器0.5间距16PIN翻盖式双侧触点上下接
30-150	± 0.35	PART NO.	LAIL-FPC-CDX01-16P0.5-GW
10-30	± 0.2	DWG. NO.	
5-10	± 0.15		
0-5	± 0.1		
ANGLE		UNITS	mm
$\pm 3^{\circ}$		Projection	