





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE


技术要求(Technical Index):

1. 材质与表面处理(Material And Finish):
基座 (Housing) and 盖子 (Cover): LCP UL94V-0 Nature Or Black;
端子 (Terminal) :Phosphor Copper Au/Sn Plated;
焊片 (Solder) : Copper Alloy Au/Sn Plated;
2. 工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
3. 额定电压(Rated voltage): 50V, AC/DC.
4. 额定电流: 0.4A, AC/DC.
5. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
6. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
7. 耐电压(Withstanding Voltage): 200V AC/minute.


10PIN



SECTION A-A



适用扁平电缆



PCB Layout

COSTOMTER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING			TITLE	FPC连接器0.5间距10PIN抽层式上接（贴片）	REV.	A
CHECKED						
APPROVED						
TOLERANCES ARE			PART NO.	LAIL-FPC-BS01-10P0.5-W	UNITS	mm
30-150	±0.35	ANGLE				
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			DWG. NO.		Projection	