



ROHS





PCB Layout

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

8PIN

技术指标 (Technical Index):

1. 塑件材质: LCP UL94-V0
2. 端子材质: 磷青铜, 镀锡/镀金
3. 焊片材质: 磷青铜, 镀锡/镀金
4. 温度范围 (Temperature range): -25° C~85° C.
5. 额定电压 (Rated voltage): 50V, AC/DC (=等效).
6. 接触电阻 (Contact resistance): $\leq 0.03\Omega$.
7. 绝缘电阻 (Insulation resistance): $\geq 500M\Omega$.
8. 耐压: 200V/1 Minute.



适用扁平电缆线

CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司	
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD	
CHECKED				
APPROVED				
TOLERANCES ARE			TITLE	FPC连接器0.5间距8PIN抽层式单侧触点/垂直 (立贴)
30-150	±0.35	ANGLE	PART NO.	LAIL-FPC-BL01-8PO. 5-LT
10-30	±0.2		UNITS	mm
5-10	±0.15		DWG. NO.	
0-5	±0.1		Projection	