







ROHS

39PIN



Recommended PCB mounting pattern and metal mask dimensions

Recommended metal mask thickness: $t=0.1$



Recommended FPC/FFC Dimensions

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

Note:

1.Material

- 1.1: Housing: LCP UL94-V0 Color: White
- 1.2: Actuator: LCP OR PA UL94-V0 Color:Black.
- 1.3: Contact: Phosphor Bronze.
- 1.4: LEG: Phosphor Bronze.

2.Plating

- 2.1: Contact: See Part Number.
- 2.2: LEG: Matte Tin Plating Over Nickel.

3.Rating:

- 3.1: Operating Voltage: 30V AC/DC.
- 3.2: Current Rating: 0.2A AC/DC.
- 3.3: Operating Temperature: -55°C~+85°C.

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司	
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD	
CHECKED			
APPROVED			
TOLERANCES ARE		TITLE	FPC连接器0.3间距39PIN翻盖式双侧触点上下接
30-150	±0.35	PART NO.	LAIL-FPC-CDX01-39P0.3-W
10-30	±0.2	UNITS	mm
5-10	±0.15	DWG. NO.	
0-5	±0.1	Projection	Projection