



ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



技术要求 (Technical Index):

1. 材质与表面处理 (Material And Finish):
基座 (Housing) 和 盖子 (Cover): LCP UL94V-0 Nature Or Black;
端子 (Terminal): Phosphor Copper Au/Sn Plated;
焊片 (Solder): Copper Alloy Au/Sn Plated;
2. 工作温度 (Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
3. 额定电压 (Rated voltage): 50V, AC/DC.
4. 额定电流: 0.4A, AC/DC.
5. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
6. 绝缘电阻 (Insulation resistance): $\geq 500\text{M}\Omega$.
7. 耐电压 (Withstanding Voltage): 200V AC/minute.

60PIN



SECTION A-A



PCB LAYOUT

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING		TITLE FPC连接器0.5间距60PIN翻盖下接H2.0 卧贴		REV. A		
CHECKED						
APPROVED						
TOLERANCES ARE		PART NO. LAIL-FPC-CX01-60P0.5-W	UNITS mm	Projection		
30-150	±0.35					ANGLE ±3°
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		DWG. NO.				