





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- 技术指标(Technical Index):
1. 塑件材质: LCP UL94-V0
 2. 端子材质: 磷青铜, 镀锡/镀金
 3. 焊片材质: 磷青铜, 镀锡/镀金
 4. 温度范围(Temperature range): -25° C~85° C.
 5. 额定电压(Rated voltage): 50V, AC/DC(=等效).
 6. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
 7. 绝缘电阻(Insulation resistance): $\geq 500M\Omega$.
 8. 耐压: 200V/1 Minute.

24PIN



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED		TITLE		REV.	A
APPROVED		PART NO.		UNITS	mm
TOLERANCES ARE		DWG. NO.		Projection	
30-150	±0.35	ANGLE	±3°		
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				