





ROHS




PCB Layout

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

15PIN




SECTION A-A



技术要求 (Technical Index):

1. 材质与表面处理 (Material And Finish):
基座 (Housing) and 盖子 (Cover): LCP UL94V-0 Nature Or Black;
端子 (Terminal): Phosphor Copper Au/Sn Plated;
焊片 (Solder): Copper Alloy Au/Sn Plated;
2. 工作温度 (Temperature range): -25° C~+85° C.
3. 额定电压 (Rated voltage): 50V, AC/DC.
4. 额定电流: 0.5A, AC/DC.
5. 接触电阻 (Contact resistance): ≤20mΩ.
6. 绝缘电阻 (Insulation resistance): ≥800MΩ.
7. 耐电压 (Withstanding Voltage): 500V AC/minute.



COSTOMER DRAWING		深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING		TITLE		FPC连接器 L 0间距15PIN插屏式半圆触点/垂直（立贴）	REV.	A
CHECKED						
APPROVED						
TOLERANCES ARE		ANGLE	PART NO.	LAIL-FPC-BL01-15P1.0-LT	UNITS	mm
30-150	±0.35					
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		±3°	DWG. NO.		Projection	