






ROHS



10PIN

- 技术要求 (Technical Index):
1. 材质与表面处理 (Material And Finish):
基座 (Housing) 和 盖子 (Cover): LCP UL94V-0 Nature Or Black;
端子 (Terminal): Phosphor Copper Au/Sn Plated;
焊片 (Solder): Copper Alloy Au/Sn Plated;
 2. 工作温度 (Temperature range): -25° C~+85° C.
 3. 额定电压 (Rated voltage): 50V, AC/DC.
 4. 额定电流: 0.5A, AC/DC.
 5. 接触电阻 (Contact resistance): ≤20mΩ.
 6. 绝缘电阻 (Insulation resistance): ≥800MΩ.
 7. 耐压 (Withstanding Voltage): 500V AC/minute.



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司	
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD	
CHECKED			
APPROVED			
TOLERANCES ARE		TITLE	FPC连接器1.0间距10PIN抽屉式单侧触点/垂直(立贴)
30-150	±0.35	PART NO.	LAIL-FPC-BL01-10P1.0-LT
10-30	±0.2	UNITS	mm
5-10	±0.15	DWG. NO.	
0-5	±0.1	Projection	