





ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- 技术指标(Technical Index):
1. 塑件材质: LCP UL94-V0
 2. 端子材质: 磷青铜, 镀锡/镀金
 3. 焊片材质: 磷青铜, 镀锡/镀金
 4. 温度范围(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
 5. 额定电压(Rated voltage): 50V, AC/DC(=等效).
 6. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
 7. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
 8. 耐压: 200V/1 Minute.

14PIN



SECTION A-A



PCB Layout

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLE	FPC连接器1.0间距14PIN抽屉式下接（卧贴）	REV.	A
CHECKED					
APPROVED					
TOLERANCES ARE		PART NO.	LAIL-FPC-BX01-14P1.0-W	UNITS	mm
30-150	±0.35				
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
		DWG. NO.		Projection	