







PCB 参考安装方式

NOTES:
备注

1. Brass or purple copper, tin-plating
   黄铜，镀锡
2. Wire screw hole M8(M4, M5, M6)
   压线螺孔M8(M4, M5, M6)可定制
3. Current Rating: 250A
   额定电流:250A
4. There shall be no defects such as pin deformation and burrs.
   不得有脚变形，毛刺等缺陷
5. Unmarked dimensions refer to tolerances
   未标注的尺寸参考公差
6. 扭矩：3.39Nm

Ordering Information

HC - * ** * * - **** - * *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series		Product No.	Material
I=Full Teeth (齿牙)	0=0.8mm	3=M3（螺牙）	0=0个	0808=8x8mm	H=HP	产品序号	默认=Copper（黄铜）
H=Short Nut (铆螺母)	1=1.0mm	4=M4（螺牙）	1=1个	1620=16x20mm	S=SHF		RC=Red Copper（紫铜）
R=Short Gasket (铆垫片)	2=1.2mm	5=M5（螺牙）	2=2个	.....	F=Flag Hip		
	3=1.5mm	6=M6（螺牙）	3=3个				
	4=1.8mm		4=4个				
	5=2.0mm		5=5个				
	6=2.2mm		.....				

			GENERL TOLERANCE	制 图 DRAWING	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
			DIM TOL	审 核 CHECK				
			5 or more ±0.35	批 准 APPROVAL		产品名称 TITLE	PCB 焊接端子 厚度2.0 贴片 铆螺母 M8 2焊脚 54x15.2x7.9mm	版 本 REV. A
			2~5 ±0.25	比 例 SCALE		产品料号 PART NO.	HC-RN2082-5415-S916-07	单 位 UNITS mm
1	初版发行		0~2 ±0.15	投 影 Projection		材 料 MATERIAL		页 次 SHEET 1/1
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°					

深圳市华灿天禄电子有限公司 工程专用章