




PCB 参考安装方式

NOTES:
备注

1. Brass or purple copper, tin-plating
   黄铜，镀锡
2. Wire screw hole M8(M4,M5,M6)
   压线螺孔M8(M4,M5,M6)可定制
3. Current Rating: 250A
   额定电流:250A
4. There shall be no defects such as pin deformation and burrs.
   不得有脚变形，毛刺等缺陷
5. Unmarked dimensions refer to tolerances
   未标注的尺寸参考公差
6. 扭矩：3.39Nm

Ordering Information

HC - * ** * * - **** - * *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series		Product No.	Material
1=Full Teeth (齿牙)	0=0.8mm	2=M2 (螺牙)	0=0个	0303=3x3mm	1=DIP	产品序号	默认=Copper (黄铜)
2=Insert Nut (铆螺母)	1=1.0mm	3=M3 (螺牙)	1=1个	1620=16x20mm	2=SMT		RC=Red Copper (紫铜)
3=Insert Gasker (铆垫片)	2=1.2mm	4=M4 (螺牙)	2=2个	.....	3=Flag Dip		
	3=1.5mm	5=M5 (螺牙)	3=3个				
	4=1.6mm	6=M6 (螺牙)	4=4个				
	5=2.0mm		5=5个				
	6=2.3mm		.....				

深圳市华灿天禄电子有限公司 工程专用章

序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE
1	初版发行	

GENERL TOLERANCE	
DIM	TOL
5 or more	±0.35
2~5	±0.25
0~2	±0.15
Angle	±3.0°

制 图 DRAWING	07
审 核 CHECK	
批 准 APPROVAL	
比 例 SCALE	
投 影 Projection	

深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO.,LTD

产品名称 TITLE	PCB 焊接端子 厚度2.0 贴片 铆螺母 M8 2焊脚 37x18.3x7.9mm	版 本 REV.	A
产品料号 PART NO.	HC-RN2082-3718-S917-07	单 位 UNITS	mm
材 料 MATERIAL		页 次 SHEET	1/1