







NOTES:
备注

1. Brass or purple copper, tin-plating
   紫铜，镀锡
2. Wire screw hole M6(M5, M8)
   压线螺孔M6(M5, M8)可定制
3. Current Rating: 150A
   额定电流:150A
4. There shall be no defects such as pin deformation and burrs.
   不得有脚变形，毛刺等缺陷
5. Unmarked dimensions refer to tolerances
   未标注的尺寸参考公差
6. 扭矩：2.82Nm

Ordering Information

HC - * ** * * - **** - * *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series		Product No.	Material
1=Full Teeth (齿牙) 0=Insert Nut (铆螺母) 8=Insert Gasket (铆垫片)	0=4.0mm 1=3.0mm 2=2.5mm 3=2.0mm 4=1.5mm 5=1.0mm 6=0.8mm 7=0.5mm 8=0.3mm 9=0.2mm	2=M3 (螺牙) 4=M4 (螺牙) 5=M5 (螺牙) 6=M6 (螺牙)	1=1个 2=2个 3=3个 4=4个 5=5个	0808=8x8mm 1620=16x20mm	1=HP 2=HF 3=Flag Hip	产品序号	默认=Copper (黄铜) RC=Red Copper (紫铜)

深圳市华灿天禄电子有限公司
工程专用章

序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE
1	初版发行	

GENERL TOLERANCE	
DIM	TOL
5 or more	±0.35
2~5	±0.25
0~2	±0.15
Angle	±3.0°

制 图 DRAWING	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD	
审 核 CHECK			
批 准 APPROVAL		产品名称 TITLE	PCB 焊接端子 厚度1.5 插板 铆螺母 M6 4焊脚 紫铜 17x19.4x14.2mm
比 例 SCALE		产品料号 PART NO.	HC-RN1564-1719-D741RC-07
投 影 Projection		材 料 MATERIAL	

版 本 REV.	A
单 位 UNITS	mm
页 次 SHEET	1/1