







NOTES:
备注

1. Brass or purple copper, tin-plating
   黄铜，镀锡
2. Wire screw hole M8(M5, M6)
   压线螺孔M8(M5, M6)可定制
3. Current Rating: 200A
   额定电流:200A
4. There shall be no defects such as pin deformation and burrs.
   不得有脚变形，毛刺等缺陷
5. Unmarked dimensions refer to tolerances
   未标注的尺寸参考公差
6. 扭矩：3.39Nm

Ordering Information

HC - * ** * * - **** - * *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series		Product No.	Material
Full Teeth (齿牙)	0=1.0mm	2=M2 (螺牙)	0=0个	0808=8x8mm	H=HP	产品序号	默认=Copper (黄铜)
Short Nut (铆螺母)	1=1.2mm	3=M3 (螺牙)	1=1个	1620=16x20mm	S=SHT		RC=Red Copper (紫铜)
Short Gasker (铆垫片)	2=1.5mm	4=M4 (螺牙)	2=2个	.....	F=Flag Hip		
	3=1.6mm	5=M5 (螺牙)	3=3个				
	4=1.8mm	6=M6 (螺牙)	4=4个				
	5=2.0mm		.....				

深圳市华灿天禄电子有限公司

工程专用章

序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE
1	初版发行	

GENERL TOLERANCE	
DIM	TOL
5 or more	±0.35
2~5	±0.25
0~2	±0.15
Angle	±3.0°

制 图 DRAWING	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD	
审 核 CHECK			
批 准 APPROVAL		产品名称 TITLE	PCB 焊接端子 厚度1.5 插板 铆螺母 M8 6焊脚 22x22x17mm
比 例 SCALE		产品料号 PART NO.	HC-RN1586-2222-D743-07
投 影 Projection		材 料 MATERIAL	

版 本 REV.	A
单 位 UNITS	mm
页 次 SHEET	1/1