






| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /          | /      |
| A1        | N/A     |          |                 | 2024.12.10 |        |



SCHEMATIC



PCB LAYOUT  
BOTTOM VIEW



SS13E05X

| L(MM) |
|-------|
| 2 ~10 |

|      |           |        |     |                |           |
|------|-----------|--------|-----|----------------|-----------|
| 4    | Terminal  | —      | 4   | Brass(0.30t)   | ag Plated |
| 3    | Base      | —      | 1   | Phenolic Resin |           |
| 2    | Cover     | —      | 1   | Spcc           | Natural   |
| 1    | Keystake  | —      | 1   | PA66           | Black     |
| ITEM | PAPT NAME | TER,NO | QTY | MATERIAL       | FINISHING |

|                       |             |
|-----------------------|-------------|
| RATING                | 0.3A 50V DC |
| CIRCUIT               | 1P4T        |
| CONTACT RESISITANCE   | 100MΩ MAX   |
| INSULATION RESISTANCE | 30mΩ MAX    |
| OPERATING FORCE       | 250±100gf   |
| OPERATING LIFE        | 10000       |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERAUCES |       |



|          |  |
|----------|--|
| DESIGN   |  |
| CHECKED  |  |
| APPROVED |  |

|       |       |
|-------|-------|
| VIEW: |       |
| UNIT: | mm/in |
| SIZE: | A4    |

|             |              |
|-------------|--------------|
| MODEL TYPE: | SLIDE SWITCH |
| PART NO.:   | SS13E05X     |
| DWG NO.:    |              |