

STRUCTURE (构造)

NO.	ITEM (项目)	SPECIFICATION (规格)	
1	INSULATION (胶膜)	印字膜: 20706 (60μm)	
		白膜: 105°C 60V (60μm)	
2	SUPPORTING TAPE (补强板)	225μm	Blue (蓝色)
3	CONDUCTOR (导体)	Thickness (厚度)	0.035 ±0.005
		Width (宽度)	0.65 ±0.03
4	CONDUCTOR (导体镀层)	PLATED (电镀)	锡Sn (1μm) MIN
		PLATED (电镀)	

DIMENSION (尺寸)

No. of conductors (导体数目)	N	12 P	
Pitch (间距)	P	1.0	±0.08
Span (总间距)	SP	29	±0.08
Width (总宽度)	W	31	±0.10
Margin (边缘宽度)	M	1.0	±0.10
Total length (总长度)	TL	(TL)	±3.0
Insert Thickness (插接端厚度)	T	0.32	±0.02
Surface Thickness (线身厚度)	ST	0.155	±0.03
Strip Length (裸铜长度)	S1	4.0	±0.5
	S2	4.0	±0.5
Supporting Tape Length (补强板长度)	B1	9.0	±2.0
	B2	7.0	±2.0

Material list (辅料清单)

NO.	ITEM (项目)	SPEC (规格)	QTY (数量)
1	连接器	1.0PH 30PIN组件	1PCS

技术要求:

- 使用10mm宽冲孔刀模
- 保存环境: 温度15~25°C 湿度: 30~50RH%
- 保质期: 镀金: 12个月 镀锡: 6个月
- 产品符合RoHS 2.0标准

DESIGN:	Xiaogang Hu				广东国连电子有限公司 GUANGDONG GUOLIAN ELECTRONICS CO., LTD				
CHECK:	Ke Tian								
APPROVED:	Youquan Xu			TITLE: FFC CABLE A型					
DIM	TOL	DIM	TOL	PART NO. LVDS 1. 0*30P*TL*A4/4/9/7-D-SN					
X.	±0. 25								
X. X	±0. 20	X°	±3. 0°	REV. A SCALE: N/A UNIT: mm SHEET: 1/1 					
X. XX	±0. 15	X. X°							
X. XXX		X. XX°							