








PCB REFERENCE DIAGRAM
TOLERANCE:±0.05

G-Switch Specification:

- 1.Current rated: 1.5A AC/DC
- 2.Voltage rating: 125V AC/DC
- 3.Withstanding voltage: 1000V AC for 1 min
- 4.Contact resistance: 40mΩ max.
- 5.Insulation resistance: 500MΩ min
- 6.Durability cycle: 750 Cycles
- 7.Operating temperature range: -40°C ~ +85°C

1	SHELL	COPPER ALLOY	NI PLATED
2	HOUSING	LCP	BLACK UL 94V-0
3	TERMINALS	C5210	Au6u" PLATED ON CONTACT AREA TIn PLATED ON SOLDER AREA
NO.	PARTS	MATERIAL	REMARKS



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General tolerance:
X. ±0.40
X.x ±0.30
X.xx ±0.20
Angles ±3°

Title: Horizontal RJ45 Conn Compatible With RJ11
SMT 8P8C L=18.65mm

Molde Code: GT-RJ56B-8P8C-A

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2025.04.10



REV: A0 SHEET: 1/1