






技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$

High photosynthesis 高(H)	The female seat height (H1)	The male seat height (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90



序号	品名	材质
①	0.5 Pitch双端立式BTB等座板	PA10T UL94 V-0 颜色:黑色
②	0.5 Pitch双端立式BTB等座端子	铜合金/表面点镀金
③	0.5 Pitch双端立式BTB等座簧	LCP UL94 V-0颜色:黑色

DIMENSION IN mm

TOLERANCE UNLESS OTHERWISE SPECIFIED

.X±0.5 X.*±1*

.XX±0.2 .X.*±

.XXX±0.1 .XX.*±

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd

TITLE: 0.5 Pitch双端立式BTB等(料3.0)

DWG NO. XY-DF530A-NLBMDW

PROJ.


CUSTOMER DRAWING

SIZE A4

SCALE 1:1

SHEET 1/1

REV. A



WWW.XYECNN.COM

REV.	Q'TY	ECN. NO.	APR.	DATE

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd