











REV.	ECN NO OR DESCRIPTION	REVISED	DATE



- NOTES:
1:MATERIAL:
1-1:STAINLESS STEEL THICKNE=0.08mm
2:FINISH:
2-1:SEE DETAILED LIST.
3:PRODUCT SPECIFICATIONS:
3-1:RATED CURRENT:1.0A/MAX
3-2:VOLTAGE RATING:1.50V/AC/DC/MAX
3-3:CONTACT RESISTANCE:80mΩ/MAX
3-4:OPERATING TEMPERATURE:-40°C~85°C
3-5:NORMAL FORCE OF PRESS@3.10:0.40N MIN ON CONTACT POINT.
3-6:DURABILITY:1,500 CYCLES.
4:SALT SPRAY:SEE DETAILED LIST
5:PACKING SPECIFICATION:REEL&TARE
6:DIMENSIONS MARKED ,CPK>1.33
7:ALL DIMENSIONS MARKED MUST BE CONTROLLED BY QC;
8:COMPLIANT TO RoHS&LEAD FREE

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	侧贴弹片L3.50×W1.50×H1.40Shielding Clip,SMT		
X :±0.30	X :±2°	DWN	xiong	PART NO. TXTB-002B1-0275A	
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					