



P.C.B. LAYOUT

SPECIFICATIONS

Current rating: 3A AC/DC

Voltage rating: 250V AC/DC

Contact resistance: 20mΩ max.

Withstand voltage: 800V AC/min

Insulation resistance: 1000MΩ/min.

Temperature range: -25°C~+85°C

Material:

Part No: 2~15

Post: Brass. Tin/plated

Base: Nylon66 UL94V-0/2

Poles	PART NO.	Dimension mm	
		A	B
2	W-2503S02P-0200	2.50	7.50
3	W-2503S03P-0200	5.00	10.00
4	W-2503S04P-0200	7.50	12.50
5	W-2503S05P-0200	10.00	15.00
6	W-2503S06P-0200	12.50	17.50
7	W-2503S07P-0200	15.00	20.00
8	W-2503S08P-0200	17.50	22.50
9	W-2503S09P-0200	20.00	25.00
10	W-2503S10P-0200	22.50	27.50
11	W-2503S11P-0200	25.00	30.00
12	W-2503S12P-0200	27.50	32.50

TOLERANCE TABLE

.0	±0.30
.00	±0.15
.000	±0.05

APPROVED:	DATE:	C _{kmtw} 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 2503S-XP 米黄色 (直针座)			
DRAWN: LYF	DATE: 2024-04-07	PART. NO.		W-2503SXXP-0200	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-2503-0003	REV.	A WD00