






ABIDE BY ROHS

ITEM	H	
01	4.0	
02	4.3	
03	4.5	
04	4.8	
05	5.0	
06	5.5	
07	6.0	
08	6.5	
09	7.0	
10	7.3	
11	7.5	
12	8.0	
13	8.5	
14	...	
15	20.0	

* Key size



开关示意图



PCB.circuit prohibited area

Remarks:

1. Rated current、Voltage: DC 12V 50mA
2. Contact resistance: $\leq 100\text{m}\Omega$
3. Insulation resistance: $\geq 100\text{M}\Omega$
4. The intensity of operations: $260 \pm 50\text{gf}$
5. Life requirements: 100000次
6. Withstand voltage: AC 250V 1分钟
7. All materials comply with RoHS standards

5	Button	PPA	1	Black
4	cover	SPCC	1	Copper tin
3	Shrapnel	SUS301	1	Silver coating
2	Base	PPA	1	Black
1	TERMINAL	Brass	4	Ag Plated
NO.				

单位 UNIT	mm	一般公差 TOLERANCE ARE	浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.			
绘图 DRAWN		≤ 5 $5 \sim 30$	产品名称 TITLE 轻触开关			
设计 DESIGN		$30 \sim 50$ > 50				
审核 CHECKED		图号 DRAWING NO	产品型号 MODEL 6*6*H贴片			
校准化 STANDARD		重量 WT.	产品编码 PART NO ES602X-10XX-XXX-26-A			
批准 APPROVALS		产地 PRODUCTION	视角 PROJ	比例 SCALE	页码 SHEET	1 OF 1