







REV.	ECN NO OR DESCRIPTION	REVISED	DATE

A


B

C

D



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)



3D VIEW

NOTES:

1:MATERIAL:

1-1:TITANIUM COPPER THICKNE=0.10mm

2:FINISH:

2-1:SEE DETAILED LIST.

3:PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.5A.

3-2:VOLTAGE RATING:5.0V.

3-3:CONTACT RESISTANCE:50mOHM MAX

AFTER DURABLITY AND ENVIRONMENT:ΔR=20mOHM

3-4:OPERATING TEMPERATURE:-40°C~+85°C

3-5:NORMAL FORCE:REFER TO THE FORCE PROFILE.

3-6:DURABILITY:20,000 CYCLES. YIELD NO EXCEED 0.1MM.

4:SALT SPRAY:48 HOURS(JUDGED BY ALL OUTSIDE AREA)

5:PACKING SPECIFICATION:REEL&TARE

6:DIMENSIONS MARKED □,CPK>1.33

7:DIMENSIONS MARKED W "▼" IS KEY DIMENSION.

8:COMPLIANT TO RoHS&LEAD FREE

9:PART NO.;

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	充电弹片L4.30×W1.40×H3.80 Shielding Clip,SMT			
DWN	xiong	PART NO. TXTA-380GB-0405A		
CHKD	lee	SCALE:1:1	UNIT: mm	REV: A4
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY

A

B

C

D