






ABIDE BY ROHS

TEM	H	
01	4.3	√
02	4.5	
03	5.0	
04	5.5	
05	6.0	
06	...	

* Key size



PCB. 焊接图




电 路 图

主要技术规格:

1. 额 定 值: 50mA DC12V
2. 接触电阻: $\leq 100\text{m}\Omega$
3. 操 作 力: $250 \pm 50\text{gf}$
4. 行 程: $0.3 \pm 0.1\text{mm}$
5. 绝缘电阻: $\geq 100\text{M}\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿 命: 50,000 Cycles

材料:

本体: PPA (白色)
按钮: PPA (白色)
卡件: 黄铜 (镀银)
弹片: 不锈钢 (覆银)
盖板: 铁 (镀铜锡)



单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		>0.5~2	± 0.10		
设计 DESIGN		>2~5	± 0.25	产品名称 TITLE	轻触开关
审核 CHECKED		>5~10	± 0.30	产品型号 MODEL	3*6插件
校准化 STANDARD		角度	$\pm 0.5^\circ$	产品编码 PART NO	ES320X-10XX-43X-26-A
批准 APPROVALS		图号 DRAWING NO		视角 PROJ	
		重 量 WT.		比例 SCALE	
		产地 PRODUCTION		页码 SHEET	1 OF 1