

ABIDE BY ROHS

技术参数:
Technical parameters:

线数 Poles :
2~20P
适用线规 Wire range :
AGW 32#~26#
温度范围 Temperature range :
-25℃~+85℃
适用PC板厚度 Applicable PC board thickness:
0.6~1.2 mm
额定电流 Current rating :
1.0A
额定电压 Rated voltage :
100V DC/AC
接触电阻 Contact resistance :
≤20mΩ
绝缘电阻 Insulation resistance :
≥500MΩ
耐电压 Withstand voltage :
500V AC/minute
接触点材质 Contact Material
固定片: 黄铜brass
Pin针: 黄铜brass

			ZH1.5卧贴	A-(mm)	B-(mm)
ZH1.5卧贴	A-(mm)	B-(mm)	ZH1.5WT-11A	15.00mm	19.50mm
ZH1.5WT-2A	1.50mm	6.00mm	ZH1.5WT-12A	16.50mm	21.00mm
ZH1.5WT-3A	3.00mm	7.50mm	ZH1.5WT-13A	18.00mm	22.50mm
ZH1.5WT-4A	4.50mm	9.00mm	ZH1.5WT-14A	19.50mm	24.00mm
ZH1.5WT-5A	6.00mm	10.50mm	ZH1.5WT-15A	21.00mm	25.50mm
ZH1.5WT-6A	7.50mm	12.00mm	ZH1.5WT-16A	22.50mm	27.00mm
ZH1.5WT-7A	9.00mm	13.50mm	ZH1.5WT-17A	24.00mm	28.50mm
ZH1.5WT-8A	10.50mm	15.00mm	ZH1.5WT-18A	25.50mm	30.00mm
ZH1.5WT-9A	12.00mm	16.50mm	ZH1.5WT-19A	27.00mm	31.50mm
ZH1.5WT-10A	13.50mm	18.00mm	ZH1.5WT-20A	28.50mm	33.00mm

P. C. B LAYOUT TOP VIEW

单位 UNIT	mm	一般公差 TOLERANCE ARE	ES 浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		>0~3: ±0.15		
设计 DESIGN		>3~10: ±0.2	产品名称 TITLE	WAFER针座
审核 CHECKED		>10~30: ±0.25	产品型号 MODEL	ZH1.5卧贴-NA
校准化 STANDARD		>30: ±0.3	产品编码 PART NO	ESWF-15ZX-W-XX-A-A
批准 APPROVALS		产地 PRODUCTION	视角 PROJ	比例 SCALE
				页码 SHEET
				1 OF 1

ECN NO.	REV	DATE.	NEW DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	---------------------	---------	--------	--------