










REV.	ECN NO OR DESCRIPTION	REVISED	DATE



3D VIEW



- NOTES:
- 1)MATERIAL:
1-1:STAINLESS STEEL THICKNE=0.10mm
 - 2):FINISH:
2-1:REFER TO THE SPECIFICATION DESCRIPTION TABLE.
2-2:DIMENSIONS OF PCB PAD STENCIL ARE FOR REFERENCE ONLY, CUSTOMER CAN MODIFY IT BY THEIR OWN.
 - 3):PRODUCT SPECIFICATIONS:
3-1:RATED CURRENT:1.0A/MAX
3-2:VOLTAGE RATING:1.50V/AC/DC/MAX
3-3:CONTACT RESISTANCE:80mΩ/MAX
3-4:OPERATING TEMPERATURE:-40°C~85°C
3-5:NORMAL FORCE OF PRESS@2.20MM:0.35~0.65N.
3-6:DURABILITY:1,500 CYCLES.
 - 4):SALT SPRAY:SEE DETAILED LIST
 - 5):PACKING SPECIFICATION:REEL&TARE
 - 6):DIMENSIONS MARKED ▽,CPK>1.33
 - 7):ALL DIMENSIONS MARKED ▽MUST BE CONTROLLED BY QC;
 - 8):COMPLIANT TO RoHS&LEAD FREE
 - 9):PART NO.;



RECOMMENDED PCB LAYOUT/METAL MASK T=0.10
TOLERANCE(.XX±0.05)(焊盘/钢网推荐图)
(FOR REFERENCE ONLY)

UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS: ANGLES:		TITLE 侧贴弹片 2.75×W0.95×H2.60 Shielding Clip,SMT				
X :±0.30	X :±2°	DWN	xiong	PART NO. TXTB-038B0-0361A		
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
		CUSTOMER COPY				