








UNLESS OTHERWISE
SPECIFIED TOLERANCES


DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD


TITLE 充电弹片L2.77×W1.34×H3.60 Shielding Clip,SMT
DWN xiong PART NO. TXTA-317BA-0110A
CHKD lee SCALE:1:1 UNIT: mm
APVD wang SIZE: A4 SHEET:10F 1 REV: A4

CUSTOMER COPY




RECOMMENDED PCB LAYOUT
TOLERANCE ± 0.05 (焊盘推荐图)
(FOR REFERENCE ONLY)

耳机插入示意图




Working Position



NOTES:

- 1-MATERIAL:
1-1:STAINLESS STEEL THICKNE=0.08 $\pm$ 0.03mm
- 2-FINISH:
2-1:REFER TO THE SPECIFICATION DESCRIPTION TABLE.
- 3-PRODUCT SPECIFICATIONS:
3-1:RATED CURRENT:1.5A/MAX
3-2:VOLTAGE RATING:5.0V/AC/DC/MAX
3-3:CONTACT RESISTANCE:50m Ω /MAX
3-5:OPERATING TEMPERATURE:-40°C~85°C
3-6:NORMAL FORCE OF PRESS@0.50:28gf $\pm$ 10gf.
3-7:DURABILITY:10,000 CYCLES.
- 4:SALT SPRAY:48 HOURS(JUDGED BY ALL OUTSIDE AREA)
- 5:PACKING SPECIFICATION:REEL&TARE
- 6:DIMENSIONS MARKED $\square$,CPK>1.33
- 7:ALL DIMENSIONS MARKED $\blacktriangledown$ MUST BE CONTROLLED BY QC;
- 8:COMPLIANT TO RoHS&LEAD FREE



UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X ± 0.30 X $\pm 2^\circ$
X.X ± 0.20 X.X $\pm 1^\circ$
X.XX ± 0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	充电弹片L2.77 $\times$ W1.34 $\times$ H3.60 Shielding Clip,SMT			
DWN	xiong	PART NO. TTXA-317BA-0110A		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4

CUSTOMER COPY