




SPECIFICATIONS
Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
ZX-PM1.0-1-1PU-Z	1	0.00	1.00
ZX-PM1.0-1-2PU-Z	2	1.00	2.00
ZX-PM1.0-1-3PU-Z	3	2.00	3.00
ZX-PM1.0-1-4PU-Z	4	3.00	4.00
ZX-PM1.0-1-5PU-Z	5	4.00	5.00
ZX-PM1.0-1-6PU-Z	6	5.00	6.00
ZX-PM1.0-1-7PU-Z	7	6.00	7.00
ZX-PM1.0-1-8PU-Z	8	7.00	8.00
ZX-PM1.0-1-9PU-Z	9	8.00	9.00
.....			
ZX-PM1.0-1-20PU-Z	20	(PIN-1)	(PIN)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE	料号 PART NO.	ZX-PM1.0-1-NPU-Z	版本 REV.	A						
			X. ±0.30	X.* ±5°							审核 CHECK	LEO	品名 TITLE	1.0FH H2.0 1xnPin 180度 W1.5 U型 PC2.0 6T	页次 SHEET	1/1
			X.X ±0.20	X.X* ±1°												
			X.XX ±0.10	X.XX* ±0.5°												
单位 UNITS	比例 SCALE	1:1		兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.												