



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/



16A

	for16A	for17A	for18A	for19A	for20A
DIM.A	7.30	9.10	10.20	14.20	17.00

1pcs

	for16A	for17A	for18A	for19A	for20A
DIM.B	15.00	15.00	15.00	17.10	20.20

1pcs

	for20A
DIM.D	18.00


1pcs

20A

19A

	for16A	for17A	for18A	for19A	for20A
DIM.B	12.00	14.50	15.50	17.90	15.50


1pcs



- Specifications()
- 1.Voltage rating():1000V DC
 - 2.Current rating():250A
 - 3.Withstanding voltage():3000V AC 1Min, 2mA MAX
 - 4.Insulation resistance():≥200MΩ at DC1000V
 - 5.Protection level():IP67
 - 6.Recommended screw torque():M6:4.5~5.5N.m
 - 7.Temperature range():-40 ~+125

KCT-221-25 0

16=16mm ² (	:11.00±0.40)
25=25mm ² (	:13.20±0.50)
35=35mm ² (	:14.50±0.50)
50=50mm ² (	:16.50±0.60)
70=70mm ² (	:19.00±0.60)



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW: 	MODEL TYPE: 2
CHECKED		UNIT: mm/in	PART NO.: KCT-221-250
APPROVED		SIZE: A4	DWG NO.: