

1

2

3

4



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/

A

B

C

D




KCT-210-16 0-Z

16=16mm²(:11.00±0.40)
25=25mm²(:13.20±0.50)
35=35mm²(:14.50±0.50)
50=50mm²(:16.50±0.60)
70=70mm²(:19.00±0.60)

A:A
C:C
Z:Z

CODINGS



- Specifications()
- 1.Voltage rating():1000V DC
 - 2.Current rating():250A
 - 3.Withstanding voltage():3000V AC 1Min, 2mA MAX
 - 4.Insulation resistance():≥200MQ at DC1000V
 - 5.Protection level():IP67
 - 6.Recommended screw torque():M6:4.5~5.5N.m
 - 7.Temperature range(): -40 ~+125

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.: KCT-210-160-Z
APPROVED		SIZE: A4	DWG NO.:

1

2

3

4