








PCB LAYOUT

Rating: 1.0A 30V DC
Contact Resistance: 100 mΩ Max.
Operating temperature: -20℃~70℃
Operating force: 3-20N
Operating Life: 5,000cycles

④	sleeve	—	1	Copper	Ni Plating	—
③	Shell	—	1	Phosphor bronze	Ni Plating	—
②	Terminal	—	6	Phosphor bronze	Sn Plating	—
①	Housing	—	1	PA66	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	J.X.Zhang	2025/12/4					
CHECKED				TITLE:	PHONE JACKES		
APPROVALS				PART NO.	PJ-356		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
	±2'		DRAWING NO.			SHEET 1 OF 1	

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.