

1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/

A

B

C




D

A

B

C


D



KCT-210-70 0-A

16=16mm ² (	:11.00±0.40)	A:A
25=25mm ² (	:13.20±0.50)	C:C
35=35mm ² (	:14.50±0.50)	Z:Z
50=50mm ² (	:16.50±0.60)	
70=70mm ² (	:19.00±0.60)	

CODINGS



- Specifications()
- Voltage rating():1000V DC
 - Current rating():250A
 - Withstanding voltage():3000V AC 1Min, 2mA MAX
 - Insulation resistance():≥200MΩ at DC1000V
 - Protection level():IP67
 - Recommended screw torque():M6:4.5~5.5N.m
 - Temperature range(): -40 ~+125

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.: KCT-210-700-A
APPROVED		SIZE: A4	DWG NO.:

1

2

3

4