








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/








Specifications()

- 1.Voltage rating():1000V DC
- 2.Current rating():150A (35)
- 3.Withstanding voltage():3000V AC 1Min, 2mA MAX
- 4.Insulation resistance():200MQ MIN at DC1000V
- 5.Protection level():IP67
- 6.Mating cycles 100 cycles Min
- 7.Salt spray test 5% NaCl 48H;
- 8.Temperature range():-40 ~+125

KHV-220 FR-35 AS

35=35mm²(OD:Ø14.50±0.50mm)

A:A
B:B
C:C
B:
S:



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB 星域
Connection

DESIGN
CHECKED
APPROVED

VIEW: 
UNIT: mm/in
SIZE: A4

MODEL TYPE:
2
PART NO.:
KHV-220FR-35AS
DWG NO.: