

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/

Specifications()

1.Voltage rating():1500V DC

2.Current rating():350A MAX






3.Withstanding voltage():6800V DC

4.Insulation resistance():200MΩ at DC1500V

5.Protection level():IP67

6.Mating cycles 500 cycles Min

7.Temperature range():-40 ~+125



KES-008 F R-95 A S

:
70=70mm²(:15±0.60mm)
95=95mm²(:17.30±0.60mm)
4A=4/0 AWG(:19.20±0.60mm)

N:
S:
A:A
B:B

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN		VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.: KES-008FR-95AS
APPROVED		SIZE: A4	DWG NO.: